BLUESIL TM GRS 55



distribuito da: ANDREA GALLO DI LUIGI S. r. l.

azienda fondata nel 1892

Via Erzelli, 9 - 16152 Genova (Italy) Tel. 010.650.29.41

www.andreagallo.it

Description	BLUESIL GRS 55 consists of a silicone fluid thickened with a lithium soap. It is especially designed for dynamic lubrication between rubber and metal in pneumatic systems.	
	Its formulation allows a slight swelling of the rubber, that ensures very good tightness between rubber and metal. BLUESIL GRS 55 is designed to meet the requirements of MIL G-4343 C and OTAN G 392.	
 Lubrication of toroidal joints and seals in the car industry. 		
Lubrication of rings on metallic shafts.		
Advantages	 Résistance to heat: slight lowering of viscosity with increasing temperature but does not decompose and gives a long service life. 	
	 Very little change in consistency with temperature: does not stiffen when cold, does not thin out at high temperatures. Very good stability: especially in contact with water and most corrosive media. 	
Colour	Light brown	
Specific gravity at 25 °C, approx	1.0	
Penetration, worked 1/10 ^e mm(ASTM D 217-48)	280 ± 20	
Penetration not worked during 24 hours 1/10 ^e mm, approx	270	
Bleed, after 24 hours at 100 °C, per cent; maximum (1)	5	
Volatiles after 24 hours at 100 °C, per cent ;maximum (1)	2.5	
Minimum drop point (°C), approx(ASTM D 566-42)	160	
Extremes of service temperature (°C) (approx.)	– 65 to +175	

BLUESIL GRS 55 complies with the following specifications: MIL G 4343 C and OTAN G

(1) determined with equipment described in specification MIL-S-8660 B



392

BLUESIL[™] GRS 55

Processing

Surfaces to be treated with BLUESIL GRS 55 should be carefully dusted, cleaned and degreased before application.

BLUESIL GRS 55 can be applied with tap or brush.

REMARKS:

- BLUESIL GRS 55 should not be applied to surfaces which are to be painted.
- 2. BLUESIL GRS 55 is not recommended for the lubrication of taps and valves for oxygen systems. This is because silicones in contact with oxygen under pressure may cause explosions.
- 3. Do not mix with other greases
- 4. We recommend to proceed to some compatibility tests if contacts with rubbers or plastics are expected.

Packaging BLUESIL GRS 55 is supplied in 100 g tubes, 1 kg cans and 25 kg drums. Storage and shelf life When stored in is original unopened packaging at a normal temperature between + 2 and + 40 °C, BLUESIL GRS 55 must be used within 18 months of the manufacture date shown on the packaging. Beyond this date, Bluestar Silicones no longer guarantees that the product meets the sales specifications. Furthermore, we recommend that **BLUESIL GRS 55** be stared in a cool, dry place. Safety Consult the Safety Data Sheet BLUESIL GRS 55.

Visit our website www.bluestarsilicones.com



EUROPE

Bluestar Silicones France 21 Avenue Georges Pompidou F69486 Lyon Cedex 03 **FRANCE** Tel. (33) 4 72 13 19 00 Fax (33) 4 72 13 19 88



NORTH AMERICA

Bluestar Silicones USA 2 Tower Center Boulevard Suite 1601 East Brunswick, NJ 08816-1100 **United States** Tel. (1) 732 227-2060 Fax. (1) 732 249-7000



A LATIN AMERICA

Bluestar Silicones Brazil Ltda. Av. Maria Coelho Aguiar, 215 Bloco G - 1°andar 05804-902-Sao Paulo - SP-Brazil Tel. (55) 11 37477887



ASIA PACIFIC

Bluestar Silicones Hong Kong Trading Co. Ltd 29th Floor, 88 Hing Fat Street Causeway Bay Hong Kong Tel. (852) 3106 8200 Fax (852) 2979 0241

Warning to the users

The information contained in this document is given in good faith based on our current knowledge. It is only an indication and is in no way binding, particularly as regards infringement of or prejudice to third party rights through the use of our products. BLUESTAR SILICONES guarantees that its products comply with its sales specifications. This information must on no account be used as a substitute for necessary prior tests which alone can ensure that a product is suitable for given use. Users are responsible for ensuring compliance with local legislation and for obtaining the necessary certifications and authorisations. Users are requested to check that they are in possession of the latest version of this document and BLUESTAR SILICONES is at their disposal to supply any additional information.



distribuito da: ANDREA GALLO DI LUIGI S. r. l.

azienda fondata nel 1892 Via Erzelli, 9 - 16152 Genova (Italy) Tel. 010.650.29.41

www.andreagallo.it

